



E-13

0'5 W. MONO POWER STAGE.

Mono power stage specially indicated fro small appliance. The maximum power is 1,8 W.R.M.S at 4 Ohms. Its main characteristic is based on the high quantity of appliance thanks to its reduce size and its quality. It includes protection against short-circuits, polarity inversion and connection terminals.

TECHNICAL CHARACTERISTICS.

Voltage	From 6 up to 12 VDC
Minimum consumption	10 mA.
Maximum consumption	50 mA.
Minimum Input Signal	50 mV.
Maximum Input Signal	300 mV.
Output Impedance	4 - 8 Ohms.
Frequencies Margin	30 - 18000 Hz.
0'5 W. Distorsion	0,4 %
R.M.S Power	0'5 W.
Musical Power	0'7 W.
Sizes	30 x 28 x 15 mm.

OPERATING.

MODULE'S SUPPLYING. The E-13 module had to be supplied by correctly stabilised from 6 up to 12 V. D.C., for this reason we suggest you to not use simple supply equipment neither rectifiers, which could negatively affect the module's operating , but a power supply.

We recommended you the FE-71 power supply which has been developed to perfectly answer to the circuit needs.

Connect the positive, the negative and zero of the power supply to the corresponding terminals indicated in the schedule. The distance between power supply and module have to be as short as possible (15 cm as maximum.) Verify that the assembly has been correctly done.


To obtain a correct module's operating we suggest you to protect is against mains interference, to do that you have to place between the mains and the transformer a filter (See the paragraph "Installation of the Filter").

OPERATING. See the paragraph "General wiring map". When the connections of the power supply are made, install a loudspeaker to the indicated terminal. The loudspeaker must to be 0'5 W (as minimum power). Nevertheless, we suggest you to place a loudspeaker with 1 W. (as minimum power). If you use quality loudspeaker, you could highly appreciate the assembly.

INPUT SIGNAL. The input signal could be supplied by receiver outputs as mixing desk, etc... Coud to be 50 mV. Minimum and 300 mV. Maximum. Connect input terminals indicated in the schedule, and the distance between module (power stage) and its signal supply, has to be as short as possible. Use shielded cable for this assembly.

VOLUME CONTROL. To adjust the input signal level of the power stage, modifying the volume, you have to install a 47 KOhm logarithmic potentiometer. Use shielded cable for the installation (see the paragraph "General wiring map").

INSTALLATION. To install the power stage, we suggest you to fit it into a metallic box. This last has to be enough stronger to include module and its power supply and well ventilated. Indeed, during its operating the module will heat. Connect the negative terminal of the power stage to the ground of the box chassis. Then connect the also the ground to the chassis.




POWER STAGE.


Ref. Full9807_Ang.

E-13

GENERAL WIRING MAP.



INSTALL OF THE FILTER.



TECHNICAL SUPPORT AND INFORMATION.

For any questions or more information:

By Fax. (24h.) +34.3. 432.29.95

By Mail: C/ Quetzal, 17-21, Entlo. 2º (08014) BARCELONA - SPAIN.

By E-Mail: sat@fadisel.com

Keep you invoice. For any repairing could you send this with module. Else, the module will lost the warranty.

All the module's CEBEK have **3 years of total warranty** in thechnical repairing, and spares from the date of buy.

WARRANTY

CEBEK is trade make of FADISEL S.L. more than 300 module's are available in stock for any purpose **request our CATALOGUE**, or visit our Web. www.fadisel.com

**3
YEARS**

**MORE 300
MODULES.**